


Cu/CuSO₄- Electrode (CSE)

General Informationen

The CSE half cell is suitable for measuring open circuit potentials on concrete surfaces. It is very solid and can be conditioned easily by the user. We recommend to use it with a shielded cable and an attached gold plated plug.



Specification

- Diaphragm: cork
- electrode body of transparent plastic material
- 4 mm gold plated socket

Options

- electrode with protecting cap
- on request with different socket
- on request with attached cable
- on request refill set or special filling for long term use

Storage

The electrode shall be stored in saturated CuSO₄- solution and be prevented from drying out.

Service

- calibration
- regeneration